



BETA 666/C2

Zero-Reset click-type wrench, in case, with sockets and extension bars



Certifications and Standards



UNI EN ISO 6789

Features

The 666/C2 provides everything you need for precision and reliable tightening with everything at hand

COMPLETE KIT FOR EVERY NEED

In addition to the torque wrench, sockets, extensions and related fittings are included in the cassette for more efficient, quicker and more versatile work.

ORDER AND CONVENIENCE

The drawer protects the tools and keeps them in perfect condition at all times, also facilitating transport.



ALL IN ONE ARTICLE

A complete assortment of Zero-Reset wrenches, sockets, extensions and fittings, supplied in a sturdy box for safe and convenient transport.



REVERSIBLE RATCHETS

72-tooth mechanism for fast and precise use of the wrench, ensuring a recovery angle of only 5°.



DOUBLE GRADUATED SCALE

High scale visibility. Easily selectable setting with extremely precise increment.

Certifications and Standards



UNI EN ISO 6789

666/2: n. ZERO-RESET click-type torque wrenches □ 5÷25 Nm
900: n. 1/4" hexagon sockets □ 4÷13 mm
900/20 - 900/20L: n. 1/4" drive extension bar 50-100 mm
900/16: n. 0 adaptor, 1/4" female and 3/8" male drives E 1/4 - B 3/8
895/1: n. 0 socket holder

Coded items

	Art.
006661002	666/C2

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

