
PRODUCT-DETAILS**TC102****MINI MTG BASE .75X.5IN NAT NYL SCR**

General Information

Extended Product Type	TC102
Product ID	7TAG009880R0001
EAN	5414363057857
Catalog Description	MINI MTG BASE .75X.5IN NAT NYL SCR
Long Description	Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.752 Inches), Width of 12.7mm (0.50 Inches), Height of 3.2mm (0.126 Inches). #8 Screw Mounting Method. Bulk Pack

Ordering

EAN	5414363057857
UPC	786210822426
Country of Origin	United Kingdom (GB) United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	12.75 in 324 mm
Package Level 2 Height	6.25 in 159 mm
Package Level 2 Depth / Length	17.5 in 445 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19670830
Material	Nylon/Polyamide 6.6
Mounting Holes	#8
Mounting Type	Screw
Process Temperature	-40 to +185 °F
Rating	
Product Name	NYLON MOUNTING BASE FOR CABLE TIE
Product Type	Mounting Base
RoHS Date	9AKK107992A8806
Special Functions	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC102
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC102
REACH Declaration	9AKK107992A3995
RoHS Information	9AKK107992A8806

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

