



BETA 7241NFT BASIC leather occupational shoe, water-repellent



Certifications and Standards



O2 FO SR

EN ISO 20347:2011

Features

The 7241NFT smooth water-repellent leather shoe with a two-density polyurethane outsole for cost-effective

FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

WATERPROOF

The high-quality smooth leather upper is perfect for protection in all weather conditions thanks to its water-repellent properties.

NEW EN ISO 20347:2022 STANDARD

The shoe is O2 FO SR certified according to the latest EN ISO 20347:2022 standard. It is ideal for less demanding work environments, thanks to improved slip and oil resistance.



FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



PROTECTIVE GUSSET

The leather gusseted tongue protects against the ingress of liquids and debris.



Certifications and Standards

CE

O2 FO SR

EN ISO 20347:2011



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	610 g
TYPE:	low

Lightness

Water-repellent leather

Comfort

Dual-density polyurethane

Safety



Felt carbon

Protections

Tip: Not available

Durability: Not available

Coded items

	Art.	EU	UK	 mm
072410735	7241NFT 35	35	2,5	228
072410736	7241NFT 36	36	3,5	235
072410737	7241NFT 37	37	4,5	242
072410738	7241NFT 38	38	5	248
072410739	7241NFT 39	39	6	255
072410740	7241NFT 40	40	6,5	262
072410741	7241NFT 41	41	7	268
072410742	7241NFT 42	42	8	275
072410743	7241NFT 43	43	9	282
072410744	7241NFT 44	44	10	288
072410745	7241NFT 45	45	10,5	295
072410746	7241NFT 46	46	11	302
072410747	7241NFT 47	47	12	308
072410748	7241NFT 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

