


# 19" Splice Box Front Panel 24 port SC Duplex violet

## Description

This front panel by Delock can be mounted in a 19" splice box by Delock.



**Item no. 43367**

EAN: 4043619433674

Country of origin: China

Package: White Box

## Technical details

- Connectors:
  - 24 x SC Duplex female >
  - 24 x SC Duplex female
- Colour: violet
- For 48 OM4 Multi-mode fibers
- Zirconia ceramic ferrule with protection cap
- For mounting in 19" splice box, 1U
- Housing colour: black
- Dimensions (LxWxH): ca. 439.0 x 39.4 x 19.5 mm


## System requirements

- Delock 19" Fiber Optic Splice Box 43348

## Package content

- 19" splice box front panel
- 6 x screw

## Images



## General

|        |                      |
|--------|----------------------|
| Style: | both sides identical |
|--------|----------------------|

## Physical characteristics

|                 |          |
|-----------------|----------|
| Housing colour: | black    |
| Depth:          | 19.5 mm  |
| Width:          | 439.0 mm |
| Height:         | 39.4 mm  |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

