

RJ45 Network Cable Cat.6A S/FTP PUR Outdoor 0.5 m black

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

With PUR (Polyurethane Reactive) cable jacket

The network cable is ideal for outdoor use and offers increased resistance to UV light, cold, moisture and dirt. In addition, the cable is characterised by its tensile strength and flexibility.



Item no. 80133

EAN: 4043619801336

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x RJ45 plug
1 x RJ45 plug
- 1:1 connected
- Cat.6A specification
- Shielded (S/FTP)
- Flexible
- Environmental temperature: -40 °C ~ 85 °C
- Cable gauge: 26 AWG
- Cable diameter: ca. 6.0 mm
- Cable jacket material: PUR
- Colour: black
- Length: ca. 0.5 m

System requirements

- A free RJ45 jack

Package content

- Patch cable

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Operating temperature:	-40 °C ~ 85 °C
------------------------	----------------

Physical characteristics

Cable gauge:	26 AWG
Shielding:	S/FTP
Length:	0.50 m
Colour:	black
Cable jacket material:	PUR

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de