

Mini DisplayPort 1.1 to DVI adapter with latch passive

Description

This mini DisplayPort adapter by Delock can be used to connect a DVI monitor to graphics cards with mini DisplayPort ports that have special notches in the slot bracket above the ports. The additional latch of the plug of the adapter snaps into the notch and prevents the adapter from being pulled out unintentionally.



15 cm

Item no. 65979

EAN: 4043619659791

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort male with latch >
 - 1 x DVI 24+5 female
- Chipset: Pericom PI3VDP411LS
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.1 specification
- Passive converter (level shifter), suitable only for graphics cards with DP++ output
- Cable gauge: 32 AWG
- Cable diameter: ca. 4.8 mm
- Contacts gold-plated
- LSOH (halogen-free)
- Resolution up to 1920 x 1200 @ 60 Hz
(depending on the system and the connected hardware)
- Cable length incl. connectors: ca. 15 cm
- Colour: black

System requirements

- A free mini DisplayPort female

Package content

- Adapter mini DisplayPort to DVI

Images



General

Specification:	DVI-D (Single Link) DisplayPort 1.1
----------------	--

Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x DVI 24+5 female with nuts

Technical characteristics

Chipset:	NXP PTN3361
Converter type:	passive (level shifter)
Maximum screen resolution:	1920 x 1200 @ 60 Hz

Physical characteristics

Cable length incl. connectors:	15 cm
Pin finishing:	gold-plated
Cable gauge:	32 AWG
Colour:	black
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de