



Technical Data

08.03.2021

HA47-HT - thick wall adhesive lined high temperature
Heat Shrinkable Tubing up to 4:1 - 1 m lengths

HA47-HT 75/20

Article Number 321-25006



Material:	Polyolefin, chemically cross-linked (PO-X)
Colour:	Black (BK)
Supplied \emptyset D min.:	75.0 mm
Recov. \emptyset d max.:	20.0 mm
Wall (WT):	4.1 mm
Shrink Ratio:	up to 4:1
Longitudinal Change After Shrinkage:	+/-10 % max
Min. Shrink Temperature - °C:	+120 °C

Test Method

Operating Temperature - °C: -55 °C to +110 °C

Dielectric Strength:	20 kV/mm
Tensile Strength:	14 MPa
Elongation at break:	400%

ASTM D2671

RoHS

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved