









Rating	16A125VAC 10A250VAC  10(4)A 125/250Vac 	Mounting Hole	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		
Switch Function	4P DPST ON-OFF		



Frame: Black, Nylon 66
 Actuator: Red, PC
 Waterproof rubber: Black, Silicone
 Terminals: Silver plated, Copper alloy
 Printed: None
 Waterproof: IP65

Circuit Diagram



Tolerances ±0.3 Unless Otherwise Specified

10/20/17	曾敏捷	改善開關裝配強度,卡耳加膠加強,耳朵形狀變更,并更新外觀圖				△
10/17/14	黃洋	依零件圖和BOM表更新本體刻字,增加220-250V標籤,更新圖面.				△
Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1824158	Model Name	ROCKER SWITCH
曾敏捷	符子明	Shin	Customer No.		Model No.	R13-244B8-02
10/20/17	10/25-17	10/26-17	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 2