



Flexible strain relief for cables
model : R4/25-WH

Dimmension	
Cable cross section (A)	4.0mm
Total length (F)	25mm
Working length (E)	20mm
Width (B)	13mm
Width (D)	9.7mm
Mounting hole (C)	Max 5.6 x 5.6mm
Maximum mounting wall thickness (G)	3mm

Other	
Material	Hydrogenated styrene butadiene block copolymer (SEBS)
	Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)
	Ethylene Propylene Diene Monomer (EPDM)
	Styrene butadiene styrene block copolymer (SBS)

