

# Han CGM-P-EXi M20 D 5...9mm



Part number	19 00 000 7101
Specification	Han CGM-P-EXi M20 D 59mm
HARTING eCatalogue	https://b2b.harting.com/19000007101

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-Ex i
Type of accessory	Cable gland

#### Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

### Technical characteristics

Limiting temperature	-40 +100 °C
Tightening torque	≤4.5 Nm (depending on the cable and the seal insert used)
Wrench size	24
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M20
Clamping range	5 9 mm
Width across corners	26.4 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 5012 (light blue) RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



## Material properties

China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

#### Commercial data

Packaging size	1
Net weight	11.7 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)