

19" Fiber Optic Patch Panel with viewing window unequipped 2U dark grey

Description

This patch panel by Delock can be mounted in a 19" rack and is ideal for quickly and securely setting up the fiber optic network in buildings.

For the installation of fiber optic adapter panels

Optical fiber adapter panels and splice cassettes can be added individually.

With viewing window

The window provides a better view of the inside of the housing.

Rear cable entry

The fiber optic cables can easily be passed through via two cable entry holes in the rear part of the panel.



Item no. 66752

EAN: 4043619667529

Country of origin: China

Package: Box

Technical details

- For mounting in 19" racks, 2U
- For optical fiber adapter panels and cassettes
- Up to 48 fibers (SC) and 96 fibers (LC)
- 2 rear cable entries
- With viewing window
- Housing colour: dark grey
- Dimensions (LxWxH): ca. 483 x 325 x 88 mm

Package content

- 19" fiber optic patch panel
- 4 x screw
- 4 x washer
- 4 x caged nut
- 4 x cable holder self-adhesive
- 8 x cable tie

Images



Physical characteristics

Length:	483 mm
Width:	325 mm
Height:	88 mm
Colour:	dark grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

