

USB 2.0 Cable USB Type-C™ male with screws to USB Type-C™ male with screws angled left / right PD 3.0 60 W 2 m

Description

This USB cable by Delock allows the connection between devices with a USB Type-C™ connector and a PC or laptop with a free USB Type-C™ port. The screws of the USB Type-C™ connector secure the connection and prevent accidental unplugging of the cable.



Item no. 80957

EAN: 4043619809578

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 USB Type-C™ male with screws on the sides
 - 1 x USB 2.0 USB Type-C™ male angled with screws on the sides
- Screw type: M2 x 0.4
- Screw distance: 15 mm
- Cable gauge:
 - 30 AWG data line
 - 24 AWG power line
- Output current: up to 3 A
- USB Power Delivery (USB PD 3.0) support up to 60 watt
- Cable diameter: ca. 3 mm
- Data transfer rate up to 480 Mbps
- Colour: black
- Length incl. connectors: ca. 2 m

Package content

- USB cable

Images



General

Specification:	USB 2.0 USB Power Delivery 3.0
Style:	both sides identical

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	30 AWG data line 24 AWG power line
Screw distance:	15 mm
Screw type:	M2
Length:	2 m
Colour:	black
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de