

RJ45 Network Cable Cat.6A plug to plug with robust latch for industrial use U/UTP Slim 2 m white

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.

With robust latch

The robust RJ45 plug is ideal for industrial applications where plugs must be plugged and unplugged frequently. Compared to conventional plugs, the industrial plug can be plugged and unplugged up to 2,000 times without the latching lug will be bent or breaking off.



Item no. 80360

EAN: 4043619803606

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug
 - 1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- U/UTP
- RJ45 plug with robust latch
- Up to 2,000 plug and bending cycles
- Slim
- Cable gauge: 28 AWG
- Contacts gold-plated: 50 µ"
- Cable diameter: ca. 3.6 mm
- Operating temperature: -20 °C ~ 60 °C
- Cable jacket material: LSZH (halogen-free)
- Colour: white
- Length: ca. 2 m

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Physical characteristics

Cable gauge:	28 AWG
Material:	LSZH (halogen-free)
Shielding:	U/UTP
Length:	2 m
Colour:	white
Cable diameter:	3.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de