

CONSTANT VOLTAGE POWER SUPPLY 24V 60W PFC



IP20 Designed for indoor use
 Protections: Short circuit, Overload, Over temperature
 Cooling by free air convection
 100% full load burn-in test
 Warranty 5 years
 Dimensions: 170mm - 45mm - 28mm
 Weight: 0,22kg

Specification

Parameter	Value
Symbol	MVL-60-24
EAN13	5901289758765
ETIM CLASS	DC-power supply
Rated supply voltage [V]	200-240V AC 50/60Hz
Power output [W]	60
Output voltage	24
Max. output current [A]	2.5
Degree of protection	IP20
Efficiency [%]	87
Power factor	>0.95
Housing	Plastic housing
Protection class	II
Suitable for outdoor use	no
Length [mm]	170
Width [mm]	45
Height/depth [mm]	28
Weight [kg]	0.27

Dimensions

