

RJ45 flat network cable with braided coating Cat.6A U/FTP 0.3 m blue

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

Super flexible and flat

The RJ45 cable is ideal for laying under carpets, floors or behind wallpaper. The material of the cable sheath is flexible and makes the cable very resistant to strain.

With braided jacket

The jacket provides excellent resistance to abrasion and protects the network cable from kinks and breaks. Thus, the cable remains durable.



Item no. 80381

EAN: 4043619803811

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x RJ45 plug
1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- Shielded (U/FTP)
- Flat
- Flexible
- With braided jacket
- Cable gauge: 32 AWG
- Contacts gold-plated: 50 µ"
- Cable size: ca. 6.4 x 2.3 mm
- Cable jacket material: nylon braid
- Colour: blue
- Length: ca. 0.3 m

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Physical characteristics

Cable gauge:	32 AWG
Material:	Nylon braid
Shielding:	U/FTP
Length:	0.3 m
Colour:	blue

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de