

Product Datasheet

Item No.: 822243

PRODUCT NAME

Xperts extension reel with 3-way IP44 socket 25 m H07RN-F 3G2,5 IP44 "F"



Reference image

Technical data

EAN	4059948004287
Weight [kg]	7.75
Dimensions	22x39,7x31,2 cm
Main color	black
Series	Xperts
Category	Cable reels
Subcategory	Extension reels
Cable type	H07RN-F
Cross section [mm ²]	3G2,5
Cable color	black
Cable length [m]	25
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	285 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44 with 25 m H07RN-F 3G2,5
Output	3x rubber shock-proof connector with protective cap 230 V, 16 A, IP44 "F"
Total number of sockets	3
Number of Type E sockets (230 V)	3
Number of cores	3



- Reel body made from robust, shatter-proof special plastic with cable reel
- With stable, shock-absorbing X double-tube frame with star-grip brake
- Frame with ergonomic non-slip 2-component handle and cable guide
- With built-in thermal circuit breaker
- Perfect for roofing and scaffolding work
- Solid rubber 3-way connector for shock-proof plugs with 360° rotating safety flap lids
- With 1.5 m power cord with shock-proof plug
- Cable in red safety color
- IP44: protected against foreign bodies and splash-proof
- 230 V, 16 A, max. 3,500 W

Your partner for professional lighting and electrical products.