

# USB 5 Gbps Coiled Cable Type-A male to Type-A female 0.4 to 0.6 m black

## Description

This USB coiled cable by Delock can be used to extend a USB port.

### Coiled Cable

The coiled cable enables a flexible connection, is easy to store and unlike conventional cables, takes up less space. It also has a high restoring force and can be extended to three times its original length.



0.4 m - 0.6 m

**Item no. 90367**

EAN: 4043619903672

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 5 Gbps Type-A male
  - 1 x USB 5 Gbps Type-A female
- Data transfer rate up to 5 Gbps
- Cable gauge:
  - 28 AWG data line
  - 24 AWG power line
- Flexible
- Coiled length:
  - min.: 100 mm
  - max.: 300 mm
- Expansion ratio: 3:1
- Cable diameter: ca. 4.0 mm
- Cable jacket material: TPU
- Colour: black
- Length pulled together incl. connectors: ca. 0.4 m
- Length extended incl. connectors: ca. 0.6 m

## Package content

- USB coiled cable

---

## Images



### Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	1 x USB 5 Gbps Type-A female

### Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	0.6 m
Colour:	black
Cable diameter:	4 mm

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de