

-EUROSTAT-

COMPACT VACUUM CLEANER (and accessories)

41-098-5017_18

Truly versatile EPA vacuum cleaner/blower with advanced cleanroom hi-filtration system for factory contract cleaning and hard to reach dust & debris from ESD sensitive electronic equipment, assembly lines, R&D area's and in field-service.

Features

- Clean room vacuum cleaner, ESD-compatible
- Fully compliant to IEC 61340-5-1
- Top quality electrical and electronic components for utmost reliability and global use
- Multi-stage filter system
- Overheating protection
- Suck or blow
- Easy to move around thanks to low motor mount, wheel well protected castor and robust rear wheels



Product Specifications

Voltage:	220V
Motor:	1100W
Material:	Permanent dissipative material
Suction power:	210 mbar
Airflow:	Max. 45 l / sec
Sound Level:	Approx. 64 dB
Weight (appliance):	Approx. 6 kg
Measurements:	39 x 34 x 42.5 cm (LxWxH)
Surface resistance:	10^7 - $10^8 \Omega$
Diameter accessories:	32 mm
Cordset length:	10 m
Extraction hose lenght:	3 m
Extraction pipe lenght:	1.3 m
Capacity:	Approx. 12 Ltr

Part Number and Description of the compact vacuum cleaner

41-098-5017	Vacuum cleaner
41-098-5018	Vacuum cleaner adjustable (potentiometer)

Part Numbers and Description of the Accessories

-EUROSTAT- ACCESSORIES 888 GS EPA/ICR BLOWVAC SERIES



**FILTER GUIDE
(NO LIQUIDS !)**

Microblown (fleece). High level filtration, yet maintains suction power & airflow. Ideal for humidity controlled CR use as permits pick-up moist air and dust.

Activated carbon. Neutralizes majority smells & odours. Arrests moist from air.

HEPA = High Efficiency Particulate Air. 99.990% retention on 0.3 µ particles.

ULPA = Ultra Low Penetration Air. 99.997% retention on 0.3 µ particles.

HEPA

Exit filter (placed after motor)

41-098-0036

MT-857 ESD

HEPA

Blow assembly + connector

Extended = 1.2 m
Relaxed = 3 m

MT-863 ESD

41-098-6064 -L-

Replacement stretch hose

L = 80 cm, L = 300 cm (extended).

MT-759

Small moulded upholstery nozzle

ALU

41-098-6006

PHU-22 ESD

BRUSH GUIDE

Brush hardness : ☒ MEDIUM/HARD (indicative) ☐ MEDIUM ☐ VERY SOFT

ULPA

Exit filter (placed after motor)

41-098-0037

MT-858 ESD

Blow assembly + connector (long version)

Extended = 2.8 m
Relaxed = 9.1 m

MT-864 ESD

41-098-0033 -XL-

SUPER STRETCH

Replacement stretch hose

MT-760 XL

Large aluminium upholstery nozzle

ALU

41-098-6005

PHU-23 ESD

BRUSH GUIDE

Brush hardness : ☒ MEDIUM/HARD (indicative) ☐ MEDIUM ☐ VERY SOFT

KIT

1 x MT-851 + MT-853 + MT-857

MT-888 ISO 7

Extension hose assembly + connector

L = 85 cm, L = 350 cm (extended)

41-098-6026

PHU-18 ESD

D-Shape brush nozzle

PHU-11 ESD ☒ PHU-12 ESD ☐ PHU-13 ESD ☐

Soft rubber bulk pick up nozzle

L = 150 mm, ID = 32 mm.

41-098-6053

PHU-26 ESD

Disposable Microblown filtering bag set

10 x

41-098-0034

MT-851

KIT

1 x MT-851 + MT-853 + MT-855

MT-888 ISO 4

Mini attachment set

41-098-5009

PHU-04 ESD

41-098-6022 SOFT BRUSH
41-098-6009 MEDIUM BRUSH
41-098-6008 MEDIUM BRUSH

PHU-16 ESD

Wheeled swivel action floor nozzle with strip brushes. Width 330 mm.

PHU-27 ESD

Activated carbon jacket (MT-753 use)

MT-852

Original hose assy complete

Extended = 3 m
Relaxed = 0.9 m

MT-861 ESD

Long soft rubber nozzle

41-098-6004

PHU-05 ESD

Crevise nozzle

41-098-6003

PHU-19 ESD

Swivel action alu floor nozzle with removable brush. Width 330 mm.

ALU

41-098-0161

PHU-27 ESD

HEPA Motorfilter (placed before motor)

41-098-0035

MT-853

Super stretch hose assy complete

Extended = 8.5 m
Relaxed = 2.5 m

MT-862 ESD

41-098-6005 mediumhard
41-098-6049 medium
41-098-6044 soft

PHU-05 ESD ☐ **PHU-09 ESD** ☐ **PHU-07 ESD** ☒

Modified PHU-05 ESD
Mini crevice nozzle

41-098-6050

PHU-20 ESD

Flag (don't be sent outside electrified steel)

41-098-6062

Special mini extension rod set (2 x rod)

PHU-28 ESD

WARNING : "SE" ATTACHMENTS ARE DESIGNED TO FUNCTION IN ESD-SAFE MODE IN ESD ENVIRONMENTS OR WITH EPA MFG'S / ACCESSORIES CONNECTED TO A PROPERLY EARTHED POWER OUTLET ONLY !