

Product data sheet

712 060 3

Cable cutter D60



- For cutting single-strand, multi-strand and fine-wire aluminum and copper cables
- Also for lead-coated cables
- Not for steel wire or wire cable
- Ratchet action for high cutting performance
- Telescope arms adjust to a range of lengths
- Cutter can be opened in any cutting position
- Can be used in cramped situations as well as overhead

General

Item number	712 060 3
EAN	4049002020421
Weight	4,500 g
Dimension	610 mm
Dimension packaging	300 x 70 x 90 mm

Specifications

Finish	black-oxide finish
Max cable dia.	60 mm
Multi-conductor cable (Cu)	Cu 630 mm ²
Multi-conductor cable (AL)	Al 800 mm ²
Fine-stranded cable (Cu)	Cu 800 mm ²
Sector shaped cable (Cu)	Cu 740 mm ²
Sector shaped cable (AL)	Al 960 mm ²
Grips	2-component grips

Classification

eCl@ss 10.1	ADS511008
ETIM 7.0	EC000142
proficl@ss 7.0	EAD256c001

Spare Parts

712 061 3	Spare blade
-----------	-------------

With reservations regarding technical modifications and errors. Illustration may vary.