DIGITUS® CAT 6, modular couplers, shielded - 2 pieces

AT-AG-8-8-C6S-2

EAN 4016032495000



Modular Coupling, 8P8C, 1:1 shielded CAT6, metal housing, 2 pcs.

The modular CAT 6 coupler from DIGITUS® consists of two shielded RJ45 sockets. The assignment is "1:1".

- Technical properties:
- Housing material: ABS UL-94V-0
- Contacts coating: Nickel, gold-plated 0.5 µ
- Shielding: Tinned bronze
- PCB:FR4, UL 94V-0
- Material contacts: Phosphor bronze
- Physical properties:
- Mating cycles: ⊠ 750 (ISO/IEC 11801, IEC 60603-7-5)
- Insertion force: 30N max. (IEC 60603-7-5)
- Retention strength: 7.7 kg between jack and plug
- 2 pieces

Attributes

- Category: CAT 6

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	500	1.17	30.00	55.00	27.00	44,550.00
Packaging Unit Inside	50	0.12	14.00	25.50	10.50	3,748.50
Packaging Unit Single	1	0.00	3.20	6.00	3.60	69.12
Net single without Packaging	1	0.00	3.20	6.00	3.60	69.12

More images:



Safety notes

- Protect product from moisture
- Avoid antistatic charging when installing the product
- Observe the specifications of the raw cable manufacturer during installation

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
https://www.assmann.com
info@assmann.com