
PRODUCT-DETAILS**TC502****MINI MTG BASE .75X.5IN NAT NY SCREW**

General Information

Extended Product Type	TC502
Product ID	7TAG009870R0000
EAN	5414363058809
Catalog Description	MINI MTG BASE .75X.5IN NAT NY SCREW
Long Description	Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.752 Inches), Width of 12.7mm (0.50 Inches), Height of 3.2mm (0.126 Inches), #8 Screw Mounting Method, 100 Pack

Ordering

EAN	5414363058809
UPC	786210804828
Country of Origin	United States (US) United Kingdom (GB)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	4.4 in 112 mm
Package Level 2 Height	5.7 in

Package Level 2 Depth / Length	145 mm 7.9 in 201 mm
--------------------------------	----------------------------

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19670830
Material	Nylon/Polyamide 6.6
Mounting Holes	#8
Mounting Type	Screw
Process Temperature	-40 to +185 °F
Rating	
Product Name	TY-RAP FASTENING
Product Type	Mounting Base
RoHS Date	9AKK107992A8806
Special Functions	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC502
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC502
REACH Declaration	9AKK107992A3995
RoHS Information	9AKK107992A8806

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

