

# Ferrite



(See page 92 for material characteristics)

## Ferrite Shallow Pots With Threaded Hole

- Max operating temperature 120°C
- Mild steel pot
- Typical Applications: For height restricted applications, light lifting, holding, securing and clamping



| Product Number | Diameter mm | Thickness mm | Thread | Weight g | Pull Force kg | Units / Pack |
|----------------|-------------|--------------|--------|----------|---------------|--------------|
| E780           | 50          | 10           | M8     | 160      | 15            | 1            |
| E781           | 80          | 18           | M10    | 560      | 55            | 1            |

## Ferrite Limpet Pots with Hook

- Max operating temperature 120°C
- Mild steel pot
- Removable hook
- Typical Applications: For height restricted applications, light lifting, holding, securing and clamping

| Product Number | Diameter mm | Thickness mm | Thread | Weight g | Pull Force kg | Units / Pack |
|----------------|-------------|--------------|--------|----------|---------------|--------------|
| E890           | 46          | 10.7         | M6     | 90       | 6             | 5            |
| E891           | 56          | 10.7         | M6     | 130      | 16            | 5            |
| E892           | 66          | 10.7         | M6     | 190      | 25            | 5            |



## Ferrite Limpet Pots with Jack

- Max operating temperature 120°C
- Mild steel pot
- Removable jack
- Typical Applications: For height restricted applications, light lifting, holding, securing and clamping

| Product Number | Diameter mm | Height mm | Fixing Stud Centres PCD M6 | Central Fixing Point | Weight g | Pull Force kg | Units / Pack |
|----------------|-------------|-----------|----------------------------|----------------------|----------|---------------|--------------|
| E895           | 66          | 10.7      | 46mm - 3 holes             | M6                   | 270      | 25            | 1            |
| E896           | 76          | 12.5      | 46mm - 3 holes             | M6                   | 300      | 33            | 1            |
| E897           | 100         | 15.5      | 70mm - 3 holes             | M6                   | 610      | 55            | 1            |



With M6 tapped holes

# Heritage

## Ferrite

### Ferrite Channels

- Max operating temperature 120°C
- Mild steel body
- Ideal for door latches, holding, signage



| Product Number | Length mm | Width mm | Height mm | Plain Fixing Holes mm | Hole Centres mm | Weight g | Pull Force kg | Units / Pack |
|----------------|-----------|----------|-----------|-----------------------|-----------------|----------|---------------|--------------|
| E898/1         | 115       | 30       | 13        | 4.2                   | 80              | 250      | 8             | 5            |
| E898/2         | 130       | 30       | 13        | 4.2                   | 90              | 300      | 14            | 5            |
| E899           | 190       | 43       | 13        | 4.2                   | 110             | 550      | 48            | 2            |