

MA-DA1U-01

Adjustable desk display mounting arm with USB ports, 17"-32"

- Position your screen perfectly
- Lightweight and full-motion design
- Practical integrated USB ports in the base



Specifications

Material: Steel, plastic
 Surface finish: Electrophoresis, Powder Coating
 Color: fine texture black
 USB interface: USB 3.2 Gen 1 (5 Gbps)
 USB ports: 1x USB-C 1x USB-A
 Supported screen size: 17" 32"
 Weight capacity (per screen): 2 ~ 9 kg
 VESA compatible: 75x75, 100x100 mm
 Tilt range: +90° -90°
 Swivel range: +90° ~ -90°
 Screen rotation: +180° ~ -180°
 Installation: grommet, clamp
 Suggested desktop thickness: clamp: 10 ~ 80 mm, grommet: 10 ~ 48 mm
 Cable management: yes

Features

- Monitor desk mount with single monitor arm and integrated USB ports
- Arm rotates, extends and retracts, tilts to change reading angles, and allows to rotate display from landscape-to-portrait mode, etc
- Enables easy ergonomic positioning for reduced strain
- Practical integrated USB-ports for charging or data
- Works with almost any LCD monitor (max. 32")
- Durable adjustable gas-spring suitable for monitors up to 9 kg
- Built-in cable management for an organized and neat workspace

Packaging

Q'ty in crtn, pcs	6
Crtn volume, CUM	0.0285956
Crtn weight, kgs	15.02
Individual package size LxWxH:	378x68x156 mm
Carton size LxWxH:	388x335x220 mm
Country of origin	CN
Barcode	8716309135375
Customs code	8302500000

Package contents

Desk arm
 User manual
 Mounting tools bag

Certificates

