

USB Type-C™ Docking Station for 4 x SATA HDD / SSD

Description

This HDD / SSD Docking Station in by Delock enables an external connection of up to **four 2.5" or 3.5" SATA HDDs / SSDs** through the USB-C™ interface, as well as the simple exchange of the drives by Hot Swap.

Four bays for HDD / SSD

Up to four HDDs or SSDs can be inserted and accessed simultaneously.

USB Type-C™ connection and separate power supply

Due to the **USB Type-C™** port and the included USB-C™ cable, the docking station can easily be connected to laptops, netbooks and ultrabooks. In addition, the power supply included in the delivery content ensures a **sufficient power supply** for the storage devices used.



Item no. 63930

EAN: 4043619639304

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 4 x SATA 6 Gb/s 22 pin receptacle
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ female
 - 1 x DC jack
- Chipset: Genesys Logic GL3523, JMicron JMS578
- Function key:
 - 1 x On / Off switch
- For 2.5" and 3.5" SATA HDD / SSD
- Suitable for all SATA HDDs / SSDs up to SATA 6 Gb/s
- Data transfer rate up to:
 - SuperSpeed 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- 10 x LED indicator
- Bootable
- Dimensions (LxWxH): ca. 166 x 127 x 65 mm
- Hot Swap, Plug & Play

Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 2 A
- Output: 12 V / 6.5 A
- Ground outside, plus inside
- Dimensions:
 - inside: \varnothing ca. 2.1 mm
 - outside: \varnothing ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Chrome OS
- Linux Kernel 3.19 or above
- Mac OS 10.14.2 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-C™ port

Package content

- Docking station
- 1 x Cable USB-C™ male to USB-C™ male, length ca. 80 cm
- External power supply
- User manual

Images



General

Function:	Hot Swap Plug & Play bootable
Suitable for data medium:	2.5" 3.5" SSD or HDD
Supported operating system:	Chrome OS Linux Kernel 3.17 or above Mac OS 10.14.2 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

External:	1 x DC 12 V power connector 1 x USB 5 Gbps USB Type-C™ female
Internal:	4 x SATA 6 Gb/s 22 pin receptacle

Technical characteristics

Chipset:	Genesys Logic GL3523 JMicron JMS578
Data transfer rate:	5 Gbps

Physical characteristics

Housing material:	Plastic
Length:	166 mm
Width:	127 mm
Height:	65 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de