

PRODUCT-DETAILS

FOR180-50-9

CABLE TIE 50LB 180 WHITE FOR ROLLE



General Information

Extended Product Type	FOR180-50-9
Product ID	7TAG009630R0045
EAN	5414363022015
Catalog Description	CABLE TIE 50LB 180 WHITE FOR ROLLE
Long Description	FOR Roll Hook and Loop Tie, White Polyethylene/Nylon for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 4572.0mm (180 Inches), Width of 19.05mm (0.75 Inch), Thickness of 1.588mm (0.0625 Inch), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

Ordering

EAN	5414363022015
UPC	786210736068
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Dimensions

Product Net Width	0.75 in 19.05 mm
Product Net Depth / Length	180 in 4572 mm

Container Information

Package Level 1 Units	1 piece
Package Level 2 Units	10 piece
Package Level 2 Width	9.9 in 251 mm
Package Level 2 Height	8.4 in 213 mm
Package Level 2 Depth / Length	9.9 in 251 mm
Package Level 3 Width	12.5 in 318 mm
Package Level 3 Height	23.37 in 594 mm
Package Level 3 Depth / Length	12.5 in 318 mm

Technical UL/CSA

Flammability According to UL94	HB
--------------------------------	----

Additional Information

Brand / Label	Ty-Rap
Color	White
Effective Date	19970815
Lock Type	Velcro Fastener
Material	Polyethylene/Nylon
Product Name	NYLON HOOK AND LOOP TIE
Product Type	Hook and Loop
Special Functions	Enables quick and convenient bundling of data and fiber optic cables.
Tensile Strength	50 lb 222 N
Thickness	0.0625 in 1.588 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FOR180-50-9
Instructions and Manuals	FOR180-50-9

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5047 >> Velcro Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

