

Product Datasheet

Item No.: 811103



PRODUCT NAME

Promo cable reel 20 m H05VV-F 3G1,5 IP20 "F"



- Reel body made from robust, shatterproof special plastic
- With stable, shock-absorbing and galvanized foot frame
- With built-in thermal circuit breaker
- IP20: indoor use
- With safety plug
- With 4 shock-proof socket outlets
- 230 V, 16 A, max. 3,500 W

Reference image

Technical data

EAN	4059948000739
Weight [kg]	3.5
Dimensions	20x32,5x22,5 cm
Main color	black
Series	Action
Category	Cable reels
Subcategory	Extension reels for Indoor Use
Cable type	H05VV-F
Cross section [mm ²]	3G1,5
Cable color	black
Cable length [m]	20
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	230 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP20
Input	Shock-proof plug 230 V, 16 A, IP20 with 20 m H05VV-F 3G1,5
Output	4x shock-proof connector without cap socket insert, 230 V, 16 A, IP20 "F"
Total number of sockets	4
Number of Type E sockets (230 V)	4
Number of cores	3

Your partner for professional lighting and electrical products.



as – Schwabe GmbH Merkurstraße 10 D – 72184 Eutingen Tel. +49 7457 9 48 53 0 office@as-schwabe.de www.as-schwabe.com

Created 21.10.2025. All proprietary rights and the right to make technical changes are reserved. Reproduction is permitted only with the prior consent of as – Schwabe GmbH.