

# Eaton 200NHM2B

Catalog Number: 200NHM2B

Fuse-link, low voltage, 200 A, AC 500 V, NH2, aM, IEC, dual indicator



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series low voltage NH Fuse	200NHM2B
	<b>Packing Unit</b>
	Pack
	Case Pack
<b>EAN</b>	<b>Quantity</b>
5027590328609	3
5027590364140	24
<b>Gross Weight</b>	<b>Length</b>
1.947 kg	153 mm
16.04 kg	365 mm
<b>Width</b>	<b>Height</b>
172 mm	76 mm
320 mm	165 mm
<b>Volume</b>	<b>ERP Name</b>
2000.016 cm <sup>3</sup>	SAP-UNITY
19272 cm <sup>3</sup>	SAP-UNITY
<b>Product Length/Depth</b>	<b>Product Height</b>
150 mm	71 mm
<b>Product Width</b>	<b>Product Weight</b>
54 mm	649 g
<b>Compliances</b>	<b>Certifications</b>
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

## Electrical data

### Amperage Rating

200 A

### Voltage rating

500 V

### Voltage type

AC

### Breaking capacity

120 kA

## Product specification

### Fuse size

NH2

### Insulated metal gripping lugs (IMGL)

No

## Accessories

### Suitable for

SD2-D Single pole NH Fuse base

TD2-D Tripe pole NH Fuse base

Microswitch 170H0235

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

## Do pobrania



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. Wszelkie  
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)