

Power 160-5 18 LTX BL OF (601521850) Cordless Compressor
18V ; Cardboard box

Order no. 601521850
EAN 4061792152816



Product may differ from Image



- Light and powerful cordless compressor with brushless motor for use in interior development and on construction sites
- Oil-free piston compressor: simple transportation and reduced service requirements
- Instrument panel with easy to read manometers for tank- and working pressure
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Fittings and control elements protected in tubular frames and clearly visible
- Second battery pack can be stored directly at the compressor for work progress without interruption

Technical data

Characteristics

Battery voltage	18 V
Suction rate	120 l/min / 4.2 cfm
Filling capacity	70 l/min / 2.5 cfm
Effective delivery volume (at 80% max. pressure)	60 l/min / 2.1 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	0.7 kW / 0.9 HP
Maximum speed	2760 rpm
Tank capacity	5 l / 1.3 gal
Sound pressure level (LpA)	69.4 dB(A)
Sound power level (LwA)	92 dB(A)
Dimensions	340 x 315 x 380 mm / 13.4 x 12.4 x 15 "
Weight (including battery pack)	9.9 kg / 21.8 lbs

Noise emission

Sound pressure level	69.4 dB(A)
Sound power level (LwA)	92 dB(A)

Scope of delivery

Universal quick-action coupling
without battery pack, without charger