

External USB Sound Card with USB-A male to 2 x 3.5 mm Stereo jack Plug & Play audio adapter for PC, Laptop and Mac

Description

The sound adapter by Delock expands a computer, laptop or tablet-PC with an additional external sound card.

Compact stereo sound

The 3.5 mm stereo jack output offers a maximum **sampling rate** of **16 bit / 48 kHz**, so your favorite music can be **played in DVD audio quality**.

Microphone connector

At the 3.5 mm jack microphone input of this adapter, for example, a PC microphone can be connected and therefore high-quality **audio recordings** with a maximum sampling rate of **16 bit / 48 kHz** can be created. This makes the adapter ideal for video chats, streaming and gaming.

Plug & Play

Due to USB Plug & Play, the adapter is immediately ready for use and no driver installation is necessary. The adapter works with all common operating systems such as **Windows, Mac OS, Chrome OS, Linux** and **Android**.



Item no. 66633

EAN: 4043619666331

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x speaker 3.5 mm 3 pin stereo jack female
 - 1 x microphone 3.5 mm 3 pin mono jack female
- Up to 16 Bit / 48 kHz sampling rate for recording and playback
- Plug & Play
- Housing material: aluminium
- Colour: grey
- Dimensions (LxWxH): ca. 45.6 x 20.1 x 10.0 mm

System requirements

- Android 11.0 or above
- Chrome OS 116.0 or above
- Linux Kernel 5.11 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- PlayStation®5
- Surface Pro 9
- PC or laptop with a free USB Type-A port

Package content

- Audio adapter
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 5.11 or above Android 11.0 or above Mac OS 13.1 or above Surface Pro 9

Interface

Connector 1:	1 x USB Type-A male
Connector 2:	1 x speaker 3.5 mm 3 pin stereo jack female
Connector 3:	1 x microphone 3.5 mm 3 pin mono jack female

Technical characteristics

Sample rate:	16 Bit / 48 kHz
--------------	-----------------

Physical characteristics

Housing material:	Aluminium
-------------------	-----------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de