

USB 2.0 Data and Fast Charging Cable USB Type-C™ male to male transparent PD 3.0 100 W 3 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. The integrated E-Marker chipset supports the PD 3.0 function for fast charging with a charging power of up to 100 W. As soon as the cable is connected to a power source, a LED lights up in blue.



Quality and performance

Optically it convinces with its fine textile shielding and with its connectors in transparent housing. The high cable gauge of the power line with 22 AWG also supports a stable power supply of up to 5 A.

Item no. 80765

EAN: 4043619807659

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x USB Type-C™ male
1 x USB Type-C™ male
- Chipset: E-Marker HUSB332A
- Cable gauge:
28 AWG data line
21 AWG power line
- USB Power Delivery (USB PD 3.0) support up to 100 watt (20 V / 5 A)
- Cable diameter: ca. 3.8 mm
- Data transfer rate up to 480 Mbps
- Cable with textile shielding
- Connector with metal housing
- Colour: black
- Length: ca. 3 m

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0 USB Type-C™
Style:	both sides identical

Interface

Connector 1:	1 x USB 2.0 Type-C™ male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	30 AWG data line 21 AWG power line
Length:	3 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de