

RJ45 Network Cable with USB Type-C™ port finder function Self Tracing Cat.6A S/FTP 7.5 m orange

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

With USB-C™ port finder function

The network cable is equipped with a port finder function that enables quick and easy identification of the cable for tracing the cable route. When power is supplied to the USB Type-C™ socket, flashing LEDs on both RJ45 plugs signal their location. This patch cable is particularly suitable for use in office environments, industrial facilities and data centres.



Item no. 80415

EAN: 4043619804153

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
2 x RJ45 plug
2 x USB Type-C™ female
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- Shielded (S/FTP)
- With port finder function
- Cable gauge: 26 AWG
- Contacts gold-plated: 50 u"
- Cable diameter: ca. 6.2 mm
- Operating temperature: -20 °C ~ 60 °C
- Cable jacket material: LSZH (halogen-free)
- Colour: orange
- Length: ca. 7.5 m

Package content

- Network cables

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	2 x RJ45 Stecker
Connector 2:	2 x USB Type-C™ female

Technical characteristics

Data transfer rate:	10 Gbps
Operating temperature:	-20 °C ~ 60 °C

Physical characteristics

Cable gauge:	26 AWG
Material:	LSZH (halogen-free)
Shielding:	S/FTP
Length:	7.5 mm
Colour:	orange
Cable diameter:	6.2 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de