









NOTE :-

- 1) ALL EDGES ARE BURR FREE
- 2) NON DIMENSIONAL RADIUS - 2..3mm
- 3) TOLERANCE AS PER DIN ISO 2768-cL
- 4) ALL CORNERS ARE FILLET WELDED AND GRINDED (240 GRAINS)
- 5) FINISH - RAL GRAY 7001 STRUCTURED

PROPERTY OF RaychemRPG (P) LTD.
ALL RIGHTS RESERVED AND/OR PHOTOCOPYING THIS DOCUMENT
TO A PERSON WITHOUT RaychemRPG (P) LTD. WRITTEN AUTHORIZATION IS PROHIBITED

Sr No.	Material	UOM	Qty	NO.	REV.NO.	DESCRIPTION	DATE	DRAWN	CHECKED
1	Base Assembly		1						
1.1	Base	Nos	1	TITLE :- JUNCTION BOX ASSEMBLY 300 x 200 x 81			DATE	SIGN	NAME
1.2	Din Rail Mounting Channel	Nos	2						RRPL DESIGN
1.3	Blind NutSert M5 - SS 304 (Large Flanged)	Nos	4	MATERIAL GI STEEL 1.5mm Thick			01/04/15		MANOJ DRAWN
1.4	Bottom Sealing Cap	Nos	4				01/04/15		A.M. CHECKED
2	Lid Assembly		1	FINISH Powder Coated Grey RAL 7001					M.S. APPROVED
2.1	Lid	Nos	1						
2.2	Sealing Gasket	m	0.95	Raychem RPG (P) Limited Geat Mahal Annexe, Dr. Annie Besant Road , Worli , Mumbai 400030 Web : www.raychemrpg.com			SCALE	PARTNO.	DRG. NO.
2.3	Plastics Insert for Screw	Nos	4				REV 00		GIJB8-A
2.4	Stud EN ISO 13918-PTM6x12- A2-50 - SS 304	Nos	1	ALL DIMENSION ARE IN MM					
2.5	Oval Head Screw DIN 966 -M5x33 - SS 304	Nos	4						