

# Coaxial High Speed HDMI cable 8K 60 Hz 48 Gbps with braided coating 3 m

## Description

This high-quality High Speed HDMI cable by Delock can be used to connect devices with an HDMI interface, such as televisions, Blu-ray players, monitors or projectors. By supporting a maximum bandwidth of 48 Gbps, content can be displayed in 8K Ultra HD (7680 x 4320 @ 60 Hz) resolution.

### Dynamic HDR and Dolby® Vision support

Supporting Dynamic HDR and Dolby® Vision, the cable is ideal for home cinema and gaming applications. Colours are realistically displayed with impressive depth, brightness and contrast are optimally reproduced.

### Perfect sound with eARC support

The Delock HDMI cable supports Enhanced ARC (eARC). This allows HDMI devices such as Blu-ray players to be connected directly to the TV. The uncompressed audio signals are then transmitted directly and lossless to the connected sound system via the audio return channel.



**Item no. 81683**

EAN: 4043619816835

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors: 2 x HDMI male
- Cable gauge: 30 AWG
- Cable type: coaxial
- Cable diameter: ca. 4.8 mm
- With braided jacket
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 48 Gbps
- Resolution up to:
  - 7680 x 4320 @ 60 Hz
  - 5120 x 2880 @ 120 Hz
  - 3840 x 2160 @ 240 Hz
 (depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D
- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format

- Supports Display Stream Compression 1.2 (DSC)
- Supports Dolby® Vision
- Supports Dynamic HDR
- Supports Game Mode VRR
- Supports eARC
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Colour: black
- Length incl. connectors: ca. 3 m

---

## Package content

- HDMI cable

---

## Images



## General

Specification:	Display Stream Compression 1.2 Dolby® Vision Dynamic HDR eARC 21:9 cinema aspect ratio 1080p HFR (High Frame Rate) 3D colour sampling in 4:4:4, 4:2:2 and 4:2:0 format Game Mode VRR Dolby® TrueHD and DTS-HD Master Audio™ CEC 2.0 control commands
Style:	both sides identical

## Interface

Connector 1:	1 x HDMI male
Connector 2:	1 x HDMI male

## Technical characteristics

Data transfer rate:	up to 48 Gbps
Maximum screen resolution:	7680 x 4320 @ 60 Hz 3840 x 2160 @ 240 Hz 5120 x 2880 @ 120 Hz

## Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	3 m
Pin finishing:	gold-plated
Cable gauge:	30 AWG
Shielding:	triple
Colour:	black
Cable diameter:	4.8 mm

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de