

Product Datasheet

Item No.: 63260

as
Schwabe
TechnikProdukte

PRODUCT NAME

Portable solid rubber construction site power combination unit G-M22, 3,6 kW



Reference image



- Extremely sturdy solid rubber housing, stackable for extremely space-saving storage
- Designed for heavy-duty construction site use
- Recommended for generators according to DGUV Information 203-032
- Closed lower section of housing with 77 mm ground clearance to prevent water ingress
- Housing lid with stainless steel quick fastenings
- Touch-safe even when the lid is open – in accordance with BGV [German trade association provisions] A2
- Fuses are particularly well-protected due to their internal installation
- Additional safety can be achieved with an optional screw or padlock
- Dimensions (W x H x D): 330 x 290 x 245 mm
- IP44: protected against foreign bodies and splash-proof

Technical data

EAN	4011160632600
Weight [kg]	7.8
Dimensions	40x33x40 cm
Main color	black
Category	Personal protection range
Subcategory	Series G for emergency generator
Cable type	H07RN-F
Cross section [mm ²]	3G6
Cable color	black
Cable length [m]	2
Rated voltage [V]	230
Rated current [A]	32
Maximum power	2 kW
IP protection	IP44
Protection device	4x RCD/MCB combination 2-pole, C16 A, 30 mA, 10 kA, type A
Input	CEE plug 230 V, 32 A, 3-pole with 2 m H07RN-F 3G6
Output	4x shock-proof socket outlet 230 V, 16 A, IP44
Total number of sockets	4
Number of Type F sockets (230 V)	4

Your partner for professional lighting and electrical products.

as
Schwabe
TechnikProdukte