

Panel Mount BNC female BNC female black

Description

This BNC panel mount by Delock can be used to connect BNC cables and is suitable for installation in a housing.



Item no. 91107

EAN: 4043619911073

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors: 2 x BNC female
- Impedance: 50 Ohm
- Integrated name plate
- Panel cut-out (WxH): ca. 16.8 x 22.3 mm
- Countersink for conical screws, distance ca. 28.9 mm
- Mounting hole diameter: ca. 3.3 mm
- Screw type: #4-40 UNC
- Material: zinc diecast / plastic
- Colour: black
- Dimensions (LxWxH): 32.5 x 19.1 x 35.5 mm

Package content

- Panel Mount

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x BNC female
Connector 2:	1 x BNC female

Technical characteristics

Impedance:	50 Ohm
------------	--------

Physical characteristics

Material:	zinc diecast / plastic
Length:	32.5 mm
Width:	19.1 mm
Height:	35.5 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

