

Cable DVI 24+5 male > DVI 24+5 male 3 m black

Description

This DVI cable by Delock can be used to connect a DVI monitor or a projector to the DVI interface of a PC or laptop.



Item no. 83112

EAN: 4043619831128

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x DVI 24+5 male >
 - 1 x DVI 24+5 male
- DVI-I (Dual Link)
- DVI connector with screws
- 2 x ferrite core
- Cable gauge: 28 AWG
- Cable diameter: ca. 8 mm
- Copper conductor
- Gold-plated connectors
- Cable double shielded
- Data transfer rate up to 7.92 Gb/s
- Resolution up to 2560 x 1600 @ 60 Hz (depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 3 m

System requirements

- A free DVI interface

Package content

- DVI cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x DVI 24+5 male
Connector 2:	1 x DVI 24+5 male

Technical characteristics

Data transfer rate:	7.92 Gbps
Maximum screen resolution:	2560 x 1600 @ 60 Hz

Physical characteristics

Ferrite core:	2 x
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	28 AWG
Shielding:	double
Length:	3 m
Colour:	black
Cable diameter:	8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de