

PRODUCT-DETAILS

GRNY-187-0-C

GROMMETING EXTD .187IN BLK NY 100FT



General Information

Extended Product Type	GRNY-187-0-C
Product ID	7TAG009750R0032
EAN	5414363023661
Catalog Description	GROMMETING EXTD .187IN BLK NY 100FT
Long Description	Extruded Grommeting, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 6.85mm (0.27 Inches), Width of 6.98mm (0.275 Inches), Thickness 1.27mm (0.05 Inches), Width Maximum Panel Thickness of 4.74mm (0.187 Inches)

Ordering

EAN	5414363023661
UPC	728494083919
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	15 in 381 mm
Package Level 1 Height	1.5 in 38 mm
Package Level 1 Depth /	7 in

Length	178 mm
Package Level 2 Units	10 piece
Package Level 2 Width	14.5 in 368 mm
Package Level 2 Height	13.7 in 348 mm
Package Level 2 Depth / Length	18.2 in 462 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Panel Thickness	0.187 in 4.74 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern
Sub Brand / Label	Catamount

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GRNY-187-0-C
Instructions and Manuals	GRNY-187-0-C

Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
ETIM 8	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

