

Keystone Module coupler RJ45 jack to RJ45 jack Cat.6A shielded

Description

This module by Delock can be used to extend twisted pair cables. With its standardised dimensions it can be used for easy snap-in mounting in e.g. a Keystone patch panel, face plate or surface-mount box.



Item no. 90718

EAN: 4043619907182

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x RJ45 jack
1 x RJ45 jack
- Cat.6A specification
- Shielded
- Contacts gold-plated
- For Keystone ports with 19.2 x 14.9 mm
- Operating temperature: -20 °C ~ 75 °C
- Material: zinc diecast
- Colour: silver / white
- Dimensions (LxWxH): ca. 30.6 x 16.3 x 20.5 mm

Package content

- Keystone module

General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 jack
Connector 2:	1 x RJ45 jack

Technical characteristics

Operating temperature:	-20 °C ~ 75 °C
------------------------	----------------

Physical characteristics

Material:	zinc die cast
Shielding:	shielded
Length:	30.6 mm
Width:	16.3 mm
Height:	20.5 mm
Colour:	white silver

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

