

USB 3.0 External Hub 4 Port

Description

This USB Hub by Delock can be connected to a computer via the USB Type-A interface. It expands the computer by three USB Type-A connectors. Different USB devices such as docking stations, card reader, external enclosure etc. can be connected.



Item no. 61762

EAN: 4043619617623

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 3.0 Type-B female
 - 4 x USB 3.0 Type-A female
 - 1 x 5 V DC jack
- Data transfer rate up to:
 - SuperSpeed 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- Dimensions (LxWxH): ca. 100 x 63 x 25 mm
- Use as self-powered (with power supply) or bus-powered (without power supply)
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.8 A
- Output: 5 V / 4 A
- Ground outside, plus inside
- Dimensions:
 - inside: \varnothing ca. 1.7 mm
 - outside: \varnothing ca. 4.75 mm
 - length: ca. 9.5 mm

System requirements

- Linux Kernel 2.6 or above
- Mac OS 10.5 or above
- Windows Vista/Vista-64/7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port

Package content

- Hub USB 3.0
- USB 3.0 Type-B to Type-A cable, length ca. 1 m
- External power supply
- User manual

Images



General

Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.5 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Vista 32-bit Windows Vista 64-bit
-----------------------------	---

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	4 x USB 10 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Length:	100 mm
Width:	63 mm
Height:	25 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de