

Cable Optical Fibre LC > LC Multi-mode OM5 Uniboot 5 m

Description

This fibre optical cable by Delock can be used to connect different networking devices, e.g. a NIC with an SFP module to a switch or a media converter. Both conductors share one sheath and one boot, making the cable very space efficient. The extractor lever makes it easy to unplug from high density panels.



Item no. 85691

EAN: 4043619856916

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x LC Duplex >
1 x LC Duplex
- Multi-mode OM5 cable
- Fibre: 50/125 µm
- Zirconia ceramic ferrule with protection cap
- Uniboot connector
- Extractor lever
- Polarity changeable
- Shared outer sheath
- Cable diameter: ca. 3 mm
- In 50 Ohm mode (not for use as a single-mode cable)
- Colour: limegreen
- Cable length: ca. 5 m


System requirements

- One free LC duplex port

Package content

- Optical Fibre Cable

Images



General

Specification:	OM5
Style:	both sides identical

Interface

Connector 1:	1 x LC Duplex
Connector 2:	1 x LC Duplex

Physical characteristics

Cable colour:	lime green
Length:	5 m
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

