

Antenna Magnetic Base 1 x N jack to 1 x SMA plug ULA100 1 m outdoor black

Description

This practical antenna base by Delock is characterised by its universality. It can be used as follows:

1. standing on the table
2. magnetically adhering to metallic surfaces



1.5 m

Item no. 81492

EAN: 4043619814923

Country of origin: Taiwan

Package: White Box

Technical details

- Connectors:
Base: 1 x N jack
Cable: 1 x SMA plug
- Impedance: 50 Ohm
- Operating temperature: -40 °C ~ 85 °C
- Housing material: PC
- Colour: black
- Protection class: IP67
- Cable type: LLC200
- Cable attenuation: 1.9 dB @ 2000 MHz per meter
- Cable colour: black
- Cable length: ca. 1.5 m
- Dimensions (LxD): ca. 40.7 x 78.0 mm
- Weight: ca. 209 g

Package content

- Stand

Images



General

Mounting type:	magnetic
Suitable for outdoor:	yes

Interface

Connector 1:	1 x N female
Connector 2:	1 x SMA plug

Physical characteristics

Diameter magnetic base:	78 mm
Housing material:	PC
Weight:	209 g
Height magnetic base:	40.7 mm
Cable category:	coaxial
Cable type:	LLC200
Cable attenuation:	1.9 dB @ 2000 MHz per meter
Cable colour:	black
Cable length incl. connectors:	1.5 m
Colour:	black
Cable diameter:	2.79 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

