

Cable mini DisplayPort 1.1 male > DVI 24+1 male 0,5 m

Description

This cable by Delock can be used to connect a display with an DVI port to a PC or a laptop with mini DisplayPort interface.



0.5 m

Item no. 83987

EAN: 4043619839872

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort 20 pin male >
 - 1 x DVI 24+1 male with screws
- Chipset: NXP PTN3361
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.1a specification
- Passive cable (level shifter), suitable only for graphics cards with DP++ output
- Signal direction: mini DisplayPort input > DVI output
- Cable gauge: 32 AWG
- Cable diameter: ca. 5.5 mm
- Twisted-pair cabling
- Copper conductor
- Gold-plated connectors
- Triple shielded cable
- Data transfer rate up to 3.96 Gb/s
- Resolution up to 1920 x 1200 @ 60 Hz (depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 0.5 m

System requirements

- One free mini DisplayPort DP++ female

Package content

- Mini DisplayPort to DVI cable

Images



General

Specification:	DisplayPort 1.1
----------------	-----------------

Interface

Connector:	1 x mini DisplayPort 20 pin male 1 x DVI 24+1 male with screws
------------	---

Technical characteristics

Data transfer rate:	3.96 Gbps
Maximum screen resolution:	1920 x 1200 @ 60 Hz

Physical characteristics

Cable colour:	black
Cable length incl. connectors:	0.5 m
Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	32 AWG
Shielding:	triple
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de