



EAN-13: 5901969449686  
CAT. NO: NFU-2350



## KANABO K2 MECHANICAL KEYBOARD

### PRODUCT FEATURES:

- Linear mechanical switches - smooth and consistent keystrokes without tactile feedback, designed for speed and precision
- Closed design with non-floating keys for an elegant look and stable keys
- Hot-swap sockets for easy replacement of switches without special tools or soldering
- High-quality lubricated stabilizers for smoother key operation and minimal noise
- Dedicated software for full key function customization, including macro recording
- PBT keycaps for greater resistance to wear and tear, even with heavy use
- Laser-engraved multimedia shortcuts for quick and convenient access to multimedia
- Compatible with PS4/PS5 and XBOX consoles, enjoy the freedom to play on your favorite platforms
- Anti-ghosting function, allowing you to press up to 19 keys simultaneously without interrupting the action
- Foldable feet, allowing for angle adjustment, increasing comfort of use



### PRODUCT SPECIFICATION:

<b>Communication</b>	Wired
<b>Interface</b>	USB
<b>Key mechanism</b>	Mechanical
<b>Illumination color</b>	White
<b>Cable length</b>	160 cm
<b>Number of keys</b>	87
<b>Keys lifetime</b>	50 mln.
<b>Actuation point</b>	2 mm
<b>Actuation force</b>	50 g
<b>Response time</b>	1 ms
<b>Supported Operating Systems</b>	Android, Windows 7, Windows 8, Windows 10, Windows 11
<b>Platform</b>	Android, Microsoft XBOX One S, Microsoft XBOX One X, Microsoft XBOX Series X, Microsoft XBOX Series S, XBOX One, PC, Sony PlayStation 4, Sony PlayStation 5
<b>Included Accessories</b>	2 spare mechanical switches, Keycap/switch puller
<b>Dimensions</b>	361 x 133 x 37 mm

