Cable Optical Fibre LC > LC Multi-mode OM4 5 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.



Item no. 84643

EAN: 4043619846436

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x LC Duplex >
  1 x LC Duplex
- Multi-mode OM4 cable
- Fibre: 50/125 µm
- Ceramic ferrule with dust protection
- LS0H (halogen free)
- Colour: violet
- Cable length: ca. 5 m

System requirements

- One free LC duplex port

Package content

- Optical Fibre Cable

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Specification:	OM4
Style:	both sides identical

Interface

Connector 1:	1 x LC Duplex
Connector 2:	1 x LC Duplex

Physical characteristics

Cable colour:	violet
Cable length incl. connectors:	5 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**