

# USB Type-C™ Docking Station 4K - HDMI / VGA / USB 3.1 / SD / LAN / PD 3.0

## Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. One monitor can be operated at the **HDMI or VGA** output. **Three built-in USB ports** allow the use of peripherals, and connections for gigabit network, as well as an **SD / micro SD card reader**, complete the features.

### USB Power Delivery (USB PD 3.0) support up to 100 watt

The docking station has a **USB Type-C™ Power Delivery** port to connect the power supply of the laptop or tablet to charge it. In addition it also supplies the USB ports with power. The docking station can also be used without a power supply.

### Small sturdy helper

Due to its small dimensions and its **sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



**Item no. 87735**

EAN: 4043619877355

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ male
  - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ female
  - 1 x USB 3.0 Type-A female
  - 1 x USB 3.0 Type-A female - Battery Charging specification BC1.2
  - 1 x SD / SDHC / SDXC slot
  - 1 x Micro SD / SDHC / SDXC slot
  - 1 x HDMI-A 19 pin female
  - 1 x VGA 15 pin female
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x USB Type-C™ female (power supply)
- Resolution:
  - HDMI up to 3840 x 2160 @ 30 Hz
  - VGA up to 1920 x 1080 @ 60 Hz
  - (depending on the system and the connected hardware)
- Transmission of audio and video signals

- Input power: 1 x USB Type-C™ female max. 100 W
- Metal housing
- Cable length without connectors: ca. 15 cm
- Colour: grey
- Dimensions (LxWxH): ca. 110 x 59 x 12 mm

---

## System requirements

- Chrome OS 70.0 or above
- Linux Kernel 4.6 or above
- Mac OS 10.14.2 or above
- Windows 8.1/8.1-64/10/10-64
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ docking station
- User manual

---

## Images



## General

Supported operating system:	Chrome OS 70.0 or above Linux Kernel 4.6 or above Mac OS 10.14.2 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
-----------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------

## Interface

Output:	1 x RJ45 jack 1 x VGA 15 pin female 1 x SD slot 1 x Micro SD Slot 1 x USB Type-C™ female (data transfer) 1 x USB Type-C™ female (power supply) 1 x HDMI-A female 2 x USB 5 Gbps Type-A female
Input:	1 x USB Type-C™ male

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz 2560 x 1440 @ 60 Hz 1920 x 1080 @ 60 Hz
----------------------------	-------------------------------------------------------------------

## Physical characteristics

Colour:	grey black
---------	---------------

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de