

AV000023
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON ONE SIDE

accessories, , 2m, M23 Female (socket) 12pin Straight, Free conductor end, 10wire, Metal, Shielded


MECHANICAL FEATURES

Cable infeed of A connection	Straight
Cable length	2 m
Housing material	Metal
Number of cores	10
Suitable for trailing chain	+
Version	Connection cable

ELECTRICAL FEATURES

Number of pins of A connection	12
Shielded	+
Type of A electrical connection	M23
Type of B electrical connection	Free conductor end
Type of cable	Multi-core
Type of plug-in contact, A connection	Female (socket)

OTHER FEATURES

Flame retardant	No
-----------------	----

Other


Packaging dimensions	160mm x 30mm x 240mm
Shipping weight	0.18kg
Tariff code	85444290

Classification

ipf product group	900
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection

female connection



- 1 pink
- 2 blue
- 3 red
- 4 black
- 5 brown
- 6 green
- 7 n.c.
- 8 gray
- 9 n.c.
- 10 white/green
- 11 white
- 12 brown/green

Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.