Magnetic Coiled Cable USB 2.0 Type-A male to Pogo 4 pin male + USB Type-C™ male to Pogo 4 pin female set black 1.5 m

Description

This magnetic cable by Delock is ideal for charging and data connection of USB Type-C™ devices to USB Type-A ports such as PCs, chargers, power banks or in cars. The cable consists of two parts that are connected to each other via magnetic closure. The spiral design keeps it tidy, retracts after use and prevents cable clutter.



Item no. 90992

EAN: 4043619909926

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x USB 2.0 Type-A male
  1 x USB Type-C™ male
  1 x Pogo 4 pin male
  1 x Pogo 4 pin female
- Data transfer rate up to 480 Mbps
- Cable gauge:
  30 AWG data line
  22 AWG power line
- Output current: 3 A
- Rated voltage: max. 48 V
- Coiled length:
  min.: 200 mm
  max.: 600 mm
- Expansion ratio: 3:1
- Cable jacket material: TPU
- Colour: black
- Length incl. connectors: ca. 1.5 m

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Package content

- Magnetic cable

Images








All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Schnittstelle

Anschluss:	1 x USB Type-C™ Stecker 1 x USB 2.0 Typ-A Stecker 1 x Pogo 4 Pin Stecker 1 x Pogo 4 Pin Buchse

Technische Eigenschaften

Betriebsspannung:	48 V
Datentransferrate:	480 Mbps
Maximale Stromstärke:	3 A

Physikalische Eigenschaften

Kabellänge inkl. Anschlüsse:	1,5 m
Leiterquerschnitt:	30 AWG Datenleitung 22 AWG Stromleitung
Material:	TPU
Farbe:	schwarz

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**