

# Coiled Cable EASY-USB 2.0 Type-A male to USB Type-B male 0.5 m to 0.8 m black

## Description

This coiled cable by Delock with EASY-USB Type-A male can be plugged into the appropriated USB-A female port in both directions. Thus the male port can be used both-sided and make the plug in easily.

## Coiled Cable

The coiled cable enables a flexible connection, is easy to store and unlike conventional cables, takes up less space. It also has a high restoring force and can be extended to three times its original length.



**Item no. 90130**

EAN: 4043619901302

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A reversible male
  - 1 x USB 2.0 Type-B male
- USB-A male port usable in both directions
- Flexible
- Coiled length:
  - min.: 150 mm
  - max.: 450 mm
- Expansion ratio: 3:1
- Cable gauge:
  - 28 AWG data line
  - 24 AWG power line
- Cable diameter: ca. 4.0 mm
- Contacts gold-plated
- Cable jacket material: TPU
- Colour: black
- Length pulled together incl. connectors: ca. 0.5 m
- Length extended incl. connectors: ca. 0.8 m

## Package content

- USB coiled cable

---

## Images



### Interface

Connector 1:	1 x USB 2.0 Type-A reversible male
Connector 2:	1 x USB 2.0 Type-B male

### Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	0.8 m
Colour:	black
Cable diameter:	4 mm

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de