



Specifications - PILA LED 25W P45 E14 WW FR ND

Product description	PILA LED 25W P45 E14 WW FR ND
Dimensions	45*90
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	P45
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	30 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964752
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

