


USB 5 Gbps Cable Type-A male to USB 5 Gbps Type-A female panel-mount 25 cm

Description

This cable by Delock can be used to extend a USB connection and to connect various devices. The female ports can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a USB connector in an easily accessible position.



25 cm

Item no. 86994

EAN: 4043619869947

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-A male
 - 1 x USB 5 Gbps Type-A female with nuts for installation
- Screw type: #4-40 UNC
- Mounting hole Type-A ca. 15 x 8 mm, screw hole pitch ca. 30 mm
- Data transfer rate up to 5 Gbps
- Cable gauge:
 - 30 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 5 mm
- Colour: blue
- Length incl. connectors: ca. 25 cm

System requirements

- A free USB port

Package content

- USB panel-mount cable
- 2 screws

Images



General

Specification:	USB 5 Gbps
----------------	------------

Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	1 x USB 5 Gbps Type-A female

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Cable gauge:	30 AWG data line 24 AWG power line
Screw type:	#4-40 UNC
Length:	25 cm
Colour:	blue

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de